



February 12, 2018

New Detector Tube from Uniphos Envirotronic Pvt. Ltd.

| | |
|---------------------------|--|
| Description: | Hydrogen Peroxide |
| Part Number: | SHP-1 |
| Measuring Range: | 0.5-10 ppm |
| Tests per Box: | 5 |
| Number of Strokes: | 5 strokes, for 0.5-10 ppm |
| Time per Stroke: | 1.5 minutes |
| Discoloration: | White to brown |
| Shelf Life: | 1 year |
| Applications/Use: | <ul style="list-style-type: none"> • Hydrogen peroxide is the primary bleaching agent in natural and synthetic fibers, including cotton, rayon, silk and wool. • The pulp and paper industry uses it as a bleaching agent for pulp and in paper recycling it is a de-inking agent. • It is the most commonly used bleaching agent in the food processing industry. • In the production of printed circuit boards hydrogen peroxide is used as an etchant. • Hydrogen peroxide oxidizing properties make it useful in the fields of cosmetics and medicine as a disinfectant and cleaning agent. |
| Availability: | In stock |

| Uniphos Envirotronic Pvt. Ltd. | Uniphos Envirotronic Pvt. Ltd. | Uniphos Envirotronic Inc. |
|--|---|---|
| Marketing Office Readymoney Terrace, 167, Dr. Annie Besant Road, Worli, Mumbai 400 018, India Tel +91(22) 6123 3500 Fax +91(22) 2493 8826 www.uniphos-she.com | Factory P.O. Nahuli – 396 108 Tal. Umbergaon, Dist: Valsad, Gujarat, India Tel +91(260) 2730156 / 57 / 58 Fax +91(260) 2730160 www.uniphos-she.com | 2245 Texas Drive, Suite 300 Sugar Land, TX 77479 USA Tel +1 844.247.0450 orders.usa@uniphos-envirotronic.com www.uniphosamericas.com |